



51375EN3-965: Three Light Hall / Foyer



Dimensions:

Diameter: 16" **Overall Height:** 150 1/2"
Height: 28" **Wire:** 144" (color/Clear)
Weight: 15.5 lbs. **Chain:** 120"
Mounting Proc.: Center Lock-Up
Connection: Mounted To Box

Bulbs:

3 - LED Medium A19 9.5w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- A decorative canopy is included
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.
- Supplied with wire pre-laced through chain

Collection: Somerton

Three Light LED Hall/Foyer Fixture in Antique Brushed Nickel Finish with Satin Etched Glass Shades

UPC #:785652054761

Finish: Antique Brushed Nickel (965)

Material List:

1 Body - Steel - Undefined
 1 Chain - Steel - Undefined

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1120FS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin Etched	3					5 1/2				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1			5 1/2		

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted	A19	9.5	9.5	120v	15000	800 230°	3000	90

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	51375EN3-965	1	785652054761	18	18.4	20	3.833	19.35	175	Yes
NV Pallet		16		48	40	76	84.444	309		No