



Weight: 0.8 lbs

<b>Project:</b>	<b>Type:</b>
<b>Prepared By:</b>	<b>Date:</b>

Driver Info		LED Info	
Type	N/A	Watts	0W
120V	N/A	Color Temp	N/A
208V	N/A	Color Accuracy	N/A
240V	N/A	L70 Lifespan	N/A
277V	N/A	Lumens	N/A
Input Watts	0.00W	Efficacy	N/A

## Technical Specifications

### Listings

**UL Listed:**

Suitable for wet locations in a covered ceiling

### Construction

**IC Rated:**

Suitable for direct contact with insulation

**Housing:**

Precision die-cast aluminum

**New Construction:**

Nailer bars are provided for use with wood joist installations

**Green Technology:**

Mercury and UV free. RoHS-compliant components.

**Finish:**

Formulated for high durability and long-lasting color

### Other



**Warranty:**

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at [rablighting.com/warranty](http://rablighting.com/warranty).

**Buy American Act Compliance:**

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

## Dimensions



## Ordering Matrix

Family	Size	Shape	Housing
NDCANIC	4	R	
	4 = 4" 6 = 6"	R = Round	NDCANIC = New Construction RDCANIC = Remodeler