



LED Highbay

100HB/LED/740/ND WB DL BB 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.


Product data

General Information	
Base	EX39 [Exclusionary Mogul Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	100-250W
Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	130 °
Initial lumen (Nom)	12000 lm
Luminous Flux (Rated) (Nom)	12000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	100 W
Lamp Current (Nom)	850 mA

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-
Product Data	
Order product name	100HB/LED/740/ND WB DL BB 2/1
EAN/UPC - Product	046677478001
Order code	478008
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001851404
Net Weight (Piece)	0.885 kg

LED Highbay



Dimensional drawing



High Bay Mains 250W 4000K Down Light WB

Product	D	C
100HB/LED/740/ND WB DL BB 2/1	211 mm	252 mm


Photometric data



General Ledlighting
KIMBOSCH • VERBODEN TOEGANG TOEBAZING
1:1 2018-08
LED-Producten.nl • 020 486 2222
Page 1/1

TrueForce LED Industrial and Retail WB



TrueForce LED Industrial and Retail 100HB 740 WB



TrueForce LED Industrial and Retail 740

LED Highbay

Lifetime



LED TForce HB MV 120-100W E40 others 840 12D ND NB

LED TForce HB MV 120-100W E40 others 840 12D ND NB

