



DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5704-30

Bulkheads

Polycarbonate light for indoor and outdoor areas. Colors will not fade and parts will not corrode. UV stabilized. UL listed for wet locations. Wall mount only.

Category: Outdoor

Finish: White

Construction: Polycarbonate construction

Glass: UV stabilized ribbed frosted polycarbonate oval lens



Width: 10-1/2"

Height: 5-7/8"

Depth: 3-3/4"

Glass: 10-1/4"

Height: 5-5/8"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted Mounting strap for outlet box included Complies with "Americans with Disabilities Act" - ADA Back plate covers a standard 4" hexagonal recessed outlet box	Pre-wired 6" of wire supplied 120V	Quantity: 1 60W Medium Base Medium ceramic socket	UL-CUL Wet location listed 1 year warranty Companion fixtures are available