

MONARCH COLLECTION

Monarch 70" Fan Tannery Bronze™

300206TZ (Bronze)



Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Airflow

CFM (High)	9411.00
CFM (Low)	3750.00
RPM (High)	128.00
RPM (Low)	52.00

Certifications/Qualifications

Location Rating	CSA UL Listed Dry
-----------------	-------------------

Dimensions

Base Backplate	6.75 DIA
Chain/Stem Length	0.00"
Downrod 1	1.00 OD X 6.00"
Weight	30.80 LBS
Height	18.00"
Width	69.50"

Electrical

Amps (High)	0.80
Amps (Low)	0.43
Motor Size	212MM X 25MM
Motor Type	AC

Mounting/Installation

Interior/Exterior	Interior
Lead Wire Length	78.00
Mounting Weight	30.80 LBS

Primary Lamping

Downlight Option	Optional
Watts (High)	97.00
Watts (Low)	21.00

Product/Ordering Information

Finish	Bronze
UPC	783927543392.00

Specifications

Blade Finish 1	TEAK
Blade Finish 2	CHERRY
Blade Material	WOOD
Blade Pitch	16.00
Blade Sweep	70.00
Number of Blades	5
Blades Reversible	Yes

Kichler
7711 East Pleasant Valley Road Cleveland, Ohio 44131-8010
Toll free: 866.558.5706 or kichler.com

Notes:
1) Information provided is subject to change without notice.
All values are design or typical values when measured under laboratory conditions.
2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

KICHLER®

