



CorePro LEDtube InstantFit T5

11T5HE/34-840/IF15/G/DIM 10/1

Philips LED T5 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Product data


General Information		Lamp Current (Min)	
Cap-Base	G5 [G5]		60 mA
RoHS mark	RoHS mark	Starting Time (Nom)	0.5 s
Nominal Lifetime (Nom)	50000 h	Warm Up Time to 60% Light (Nom)	0.5 s
Switching Cycle	50000X	Power Factor (Nom)	0.9
B50L70	50000 h	Voltage (Nom)	50-80 V
Light Technical		Temperature	
Color Code	841 [CCT of 4100K (841)]	T-Ambient (Max)	45 °C
Beam Angle (Nom)	200 °	T-Ambient (Min)	-20 °C
Initial lumen (Nom)	1500 lm	T-Storage (Max)	65 °C
Luminous Flux (Rated) (Nom)	1500 lm	T-Storage (Min)	-40 °C
Rated Beam Angle	200 °	T-Case Maximum (Nom)	70 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Color Consistency	<6	Dimmable	Yes
Color Rendering Index (Nom)	82	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	900 mm
Operating and Electrical		Approval and Application	
Input Frequency	40000-110000 Hz	Energy Saving Product	Yes
Power (Rated) (Nom)	11 W		
Lamp Current (Max)	400 mA		

CorePro LEDtube InstantFit T5

Approbation Marks	UL certificate RoHS compliance
Product Data	
Order product name	11T5HE/34-840/IF15/G/DIM 10/1
EAN/UPC - Product	046677476472
Order code	476473
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001823704
Net Weight (Piece)	0.110 kg
Model Number	9290018237


Dimensional drawing




TLED 900mm HFV11.5-21W 1500lm 4000K ND

Product	D1	D2	A1	A2	A3
11T5HE/34-840/IF15/G/DIM 10/1	15.3 mm	18.4 mm	847.8 mm	854.9 mm	862 mm


Photometric data



LEDtube PLC 400mm 16-5W 2G11 840 2100lm





LEDtube 11W G5 840 200D DIM IF15



LEDtube 8W G5 830 200D DIM IF10



CorePro LEDtube InstantFit T5

Lifetime




LEDtube 8-14W G5 830-850 200D DIM IF10-21

LEDtube 8-14W G5 830-850 200D DIM IF10-21



LEDtube 8-14W G5 830-850 200D DIM IF10-21

LEDtube 8-14W G5 830-850 200D DIM IF10-21



LEDtube 8-14W G5 830-850 200D DIM IF10-21

CorePro LEDtube InstantFit T5

