



ENERGY STAR CERTIFIED Light Fixtures

Amax - Downlight Surface Mount : LED-SM6DL/XX

Specifications

ENERGY STAR Partner:	Amax Lighting, Inc.
Brand Name:	Amax
Model Name:	Downlight Surface Mount
Model Number:	LED-SM6DL/XX
Indoor/Outdoor:	Indoor/Outdoor
Fixture Type:	Downlight Surface Mount
Technology:	LED
Total Light Output (lumens):	1000
Appearance/Correlated Color Temperature (K):	3000K
Total Input Power (Watts):	15.0
Color Quality (CRI):	82
Energy Efficiency - Measured Outside the Fixture (lumens/Watt):	66.7
Power Factor:	0.97
Light Source Life (hrs):	50000
Can Size(s):	6
Special Features:	Continuously Dimmable
Light Source Connection/Base Type:	N/A
Date Available On Market:	2016-08-10
Date Certified:	2016-08-12
Markets:	United States
ENERGY STAR Certified:	Yes

Additional Model Information

„(XX may be WHT, WT, NKL, BN, BRZ, or BZ and stands for finish color)

Captured On:
04/29/2020