

## NIMBUS® PBTS INS BLK ONE SIDE TAP



- Broad wire range: 750kcmil-14
- UL Listed and CSA certified for 600 volts, 90&#176C
- Dual rated for copper or aluminum conductor
- Cold temperature rated to -45&#176C
- High dielectric strength plastisol is chemical resistant
- Black cover is UV rated
- Removable port & screw plugs
- Prefilled with De-ox
- For one input & multiple output configurations, the allowable ampacities per NEC Table 310.16 and 310.17 are as follows: # 4 - 95 Amps, 1/0 - 170 Amps, 3/0 - 225 Amps, 250 - 290 Amps, 350 - 350 Amps, 600 - 475 Amps, 750 - 535 Amps
- For multiple inputs, the inputs must be staggered with outputs to allow for ampacities to be additive per NEC Table 310.16 and 310.17
- UL File E6207

Item ID	Number of Ports	Conductor Range	Length	Width	Height	Hex Size	Standard Package Quantity	NAED/UPC Number
PBTS-3-350	3	350 kcmil-6 AWG	3.6860	2.4140	2.6200	5/16	4	0783669080049