



**MCR
SAFETY**

**9679
Memphis
Dipped
Specification Sheet**

PRODUCT DESCRIPTION:

02

FEATURES:

- 13 Gauge White Nylon Shell
- Flat Nitrile Coated Palm and Fingers
- CE Score 4121
- Color coded hem to identify sizes

APPLICATIONS:

Agriculture, Assembly Line Production, Automotive Assembly, Construction, Landscaping, Manufacturing, Warehousing



TECHNICAL DATA FOR: 9679XL

Series	Memphis	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	2
Glove Size	X - Large	EN 388 : CE Score - Puncture	1
Gauge	13 Gauge		
Material	Nylon		
Made In	China		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA


Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved



MCR
SAFETY

9679
Memphis
Dipped
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9679M	Medium	9.95	3.74	2.75	15.612 lb.	1.301
9679XS	X - Small	9.15	3.35	2.5	12.156 lb.	1.013
9679L	Large	10.35	4.02	2.75	16.620 lb.	1.385
9679XL	X - Large	10.95	4.25	2.95	18.156 lb.	1.513
9679S	Small	9.45	3.50	2.5	13.668 lb.	1.139

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved