



**MCR  
SAFETY**

# 93891PU

## UltraTech

### Cut Protection Specification Sheet

**PRODUCT DESCRIPTION:**

GO Pro with Cut Pro gloves! The 93891 combines DuPont™ Kevlar®, Synthetic Materials, and Stainless Steel construction to deliver CE cut level 5 protection! It also features a black polyurethane palm and fingers for additional grip and abrasion resistance.

**FEATURES:**

- DuPont Kevlar®, Synthetic Materials, and Stainless Steel material
- Black PU coated palm & fingers
- Superior Cut Protection with Enhanced Grip
- CE cut level 5, score = 4543
- CPPT 4

**APPLICATIONS:**

Automotive Assembly, Bottling, Canning, Glass handling, HVAC, Sheet metal industry



**TECHNICAL DATA FOR: 93891PUXL**

<b>Series</b>	UltraTech	<b>EN 388 : CE Score - Abrasion</b>	4
<b>Material Group</b>	Strings	<b>EN 388 : CE Score - Cut</b>	5
<b>Product Type</b>	Cut Protection	<b>EN 388 : CE Score - Tear</b>	4
<b>Glove Size</b>	X - Large	<b>EN 388 : CE Score - Puncture</b>	3
<b>Gauge</b>	10 Gauge	<b>ANSI Cut</b>	ANSI Cut A4
<b>Material</b>	Kevlar / Synthetic		
<b>Made In</b>	Sri Lanka		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2019 MCR Safety - All Rights Reserved




**MCR**  
SAFETY

# 93891PU

**UltraTech**

**Cut Protection  
Specification Sheet**



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
93891PUL	Large	9.85	4.13	3.35	21.804 lb.	1.817
93891PUM	Medium	9.45	3.94	3.35	26.856 lb.	2.238
93891PUXL	X - Large	10.44	4.13	3.74	31.740 lb.	2.645
93891PUXXL	XX - Large	11.18	5.15	3.60	33.324 lb.	2.777
93891PUS	Small	9.05	3.94	3.15	24.084 lb.	2.007

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2019 MCR Safety - All Rights Reserved