



**MCR
SAFETY**

VBBCL3L

Insulated Rainwear

Specification Sheet

PRODUCT DESCRIPTION:

For those applications where being seen is of the utmost importance, MCR Safety's Luminator™ Series offers you a variety of high visibility garments to fit your specific applications. The VBBCL3L is our value series ANSI/ISEA Class 3 Bomber style jacket that features a bright fluorescent lime background color for daytime high visibility and 2" silver reflective stripes for low light visibility. The black shading on the lower front and arms is dirt masking and extends wear life. The black fleece inner liner not only helps keep you warm, but adds an element of comfort that you will enjoy wearing. Other features include a detachable drawstring hood with pull stops, zipper front closure, two front zipper pockets, chest cell phone pocket, and left and right side mic-tab holders. Three inner pockets offer additional storage for belongings.



FEATURES:

- ANSI/ISEA 107-2015 Class 3, Type R compliant
- Zipper front closure
- Two zipper front outer pockets
- Three inner pockets
- Soft fleece liner and stand up collar
- Detachable drawstring hood
- Left chest cell phone pocket
- Left and right shoulder mic-tab holders
- Black shaded material in high wear areas

APPLICATIONS:

Airport , Construction, EMS, Emergency, Flagman, Landscaping, Paving, Police, Railroad, Road construction, Security, Surveyor, TSA, Transportation

TECHNICAL DATA FOR: VBBCL3LL

Series	Luminator	Lining	Polyester
Category	Insulated Rainwear	Front Closure	Zipper
Class	Class III		
Type	R- Roadway and Temporary		



MCR
SAFETY

VBBCL3L

Insulated Rainwear

Specification Sheet

Color Traffic Control Zones
Size Fluorescent Lime
Material Large
Insulated Polyester / Polyurethane
 Yes

Item No:	Chest	Sleeve	Back Length	Waist	Inseam	Color	Case Weight
VBBCL3LM	50	25	27.5	N/A	N/A	Fluorescent Lime	27.490
VBBCL3LL	54	25.5	28.5	N/A	N/A	Fluorescent Lime	28.070
VBBCL3LXL	58	26	29.5	N/A	N/A	Fluorescent Lime	31.050
VBBCL3LX2	62	26.5	30.5	N/A	N/A	Fluorescent Lime	32.540
VBBCL3LX3	66	27	31.5	N/A	N/A	Fluorescent Lime	35.830
VBBCL3LX4	70	27.5	32.5	N/A	N/A	Fluorescent Lime	37.620
VBBCL3LX5	74	28	33.5	N/A	N/A	Fluorescent Lime	38.930
VBBCL3LS	N/A	N/A	N/A	N/A	N/A	Fluorescent Lime	26.700
VBBCL3LX6	N/A	N/A	N/A	N/A	N/A	Fluorescent Lime	42.660
VBBCL3LX7	N/A	N/A	N/A	N/A	N/A	Fluorescent Lime	46.400