

4" Remodel Housing with Adjustable Lampholder - EL99RA




Features

- 4" Remodel Housing.
- Integral thermal protector guards against improper lamping.
- Four remodel clips secure housing and accommodate various ceiling thickness.
- Adjustable socket bracket allows for different lamp types/sizes and proper and consistent lamp positioning.
- Pre-wired junction box provided with 1/2" and 3/4" knockouts and with removable access plates.
- Trims sold separately.
- Lamp: 50W MAX.
- Can be retrofitted to use 120V MR16 lamps with PSA28 adapter.
- UL Listed for damp location and for feed through.

Specifications

Wattage	50W
Voltage	120V
Lamp Type	Medium Base (E26)
Damp Location	Listed

Dimensions



Technical Details

Construction:

- Housing adjusts in frame to accommodate up to 1 1/4" ceiling thickness.
- Airtight housing with gasket to restrict airflow in accordance with ASTM E-283 air-tight requirements.
- Aluminum housing for greater heat dissipation.

Installation: Designed for ceiling plenums where 2x6 joists or taller are used. Maximum hole cutout is 4 1/4". See installation sheet for detailed information.

Electrical:

- Input Voltage: 120V AC.
- Thermally protected against improper lamping.

Trims: Compatible with ELCO 4" Line Voltage PAR trims.

Lamp: Designed for use with Medium Base (E26) PAR lamps up to 50W.

Listings:

- UL Listed for Damp Location.
- UL Listed for Feed Through.
- Airtight per ASTM E-283.
- Install a JA8-2016-E lamp/luminaire for Title 24 Compliance.

Warranty: ELCO Lighting warrants products will be free from defects in materials and workmanship for a period of 3 years.

Product Numbers

Item	Description	Lamp type	Watts	Voltage
EL99RA	Non-Airtight	Medium Base (E26)	50W	120V