



A-Shape LED

12A21/PER/850/P/E26/DIM 6/1FB

Philips A-shape Dimmable LED lamps are the smart LED alternative to standard incandescents. The unique lamp design provides omi-directional light with excellent dimming performance.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	12-75W
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	250 °
Initial lumen (Nom)	1100 lm
Luminous Flux (Rated) (Nom)	1100 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	91.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	12 W
Lamp Current (Nom)	155 mA
Wattage Equivalent	75 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted (FR)
Product Data	
Order product name	12A21/PER/850/P/E26/DIM 6/1FB
EAN/UPC - Product	046677479473
Order code	479477
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001836704
Net Weight (Piece)	0.058 kg

A-Shape LED


Dimensional drawing




Bulb A21 120V 12-75W 1100lm 5000K E26 D

Product	D	C
12A21/PER/850/P/E26/DIM 6/1FB	78 mm	140 mm


Photometric data



75W E26 A21 FR 250D 850 5000K





40W E26 A19 FR



75W E26 A21 FR 250D 850 5000K

A-Shape LED

Lifetime



40W E26 A19 FR

40W E26 A19 FR

