



A-Shape LED

6.5G25/PER/827/FR/G/DIM 6/1CT


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	6.5-60W
Light Technical	
Color Code	827 [CCT of 2700K]
Initial lumen (Nom)	500 lm
Luminous Flux (Rated) (Nom)	500 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	76.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	6.5 W
Lamp Current (Nom)	52 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	35 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted (FR)
Product Data	
Order product name	6.5G25/PER/827/FR/G/DIM 6/1CT
EAN/UPC - Product	046677478872
Order code	478875
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001841104
Net Weight (Piece)	0.040 kg

A-Shape LED



Dimensional drawing




Product	D	C
6.5G25/PER/827/FR/G/DIM 6/1CT	80 mm	121 mm

Bulb G25 120V 6-60W 500lm 2700K E26 D

Photometric data





LEDbulb E26 G25 Frosted 6 827



LEDbulb E26 G25 Frosted 827

A-Shape LED

Lifetime



LEDbulb E26

LEDbulb E26

