



# SPECIFICATION SHEET

## Fan B11 Torpedo Incandescent Lamp, 2-Card

Item Number **04094**

### Specifications

Energy Used (Watts).....	60
Domestic Code .....	60B11/FAN/VR 2CD
Volts .....	120
Brightness (Lumens) .....	570
Average Rated Hours .....	1500
Life (in years)*.....	1.3
Dimmable.....	Yes
Filament Type.....	C7A
Estimated Yearly Energy Cost**.....	\$7.23
Package Type.....	Card
Country of Origin.....	China



### Physical Characteristics

Finish.....	Clear
Base.....	Medium (E26)
MOL.....	3.63"

Vibration Resistant lamps are designed for vibration service only.

\*Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/kWh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.

Used under license by Westinghouse Lighting. All Rights Reserved.