



7443593S-962: Small LED Ceiling Flush Mount



Dimensions:

Diameter: 12 1/4"
Height: 4"
Weight: 2.7 lbs.

Wire: 6" (color/Black/White)
Mounting Proc.: Key Slots
Connection: Mounted To Box
Bulb Type: Modules
Bulb Base: Integrated
Volts: 120
Watts: 14
Watts Consumed: 14
Watts Rated: 14
Hours Rated: 50000
Lumens: 1000
Bulb Temp: 3000 °K
CRI: 90

Collection: Clip Ceiling Flush Mount

UPC #:785652064302

Finish: Brushed Nickel (962)

Features:

- ENERGY STAR® Qualified
- Advanced LED technology that warms in color when dimmed (3000K - 2200K).
- Meets Title 24 energy efficiency standards
- Integrated LED fixtures that meet the high efficacy LED standards set forth in Title 24 and are listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - White

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	Satin Etched	1	G560189-619			3	11 3/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Mounting Plate	3/4			9 1/2		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	7443593S-962	1	785652064302	13.75	13.25	6.25	0.659	3.8	175	Yes
NJ Pallet		105		48	40	74	82.222	399		No
NV Pallet		105		48	40	74	82.222	399		No