



3124603EN3-962: Three Light Chandelier



Dimensions:

Diameter:	19"	Overall Height:	64"
Height:	18 3/4"	Wire:	144" (color/Clear Silver)
Weight:	8.2 lbs.	Mounting Proc.:	Center Lock-Up
		Connection:	Mounted To Box

Bulbs:

3 - LED Medium A19 9.5w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Sloped ceiling mounting hardware included
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.

Material List:

- 1 Body - Steel - Brushed Nickel
- 1 6" Stem - Steel - Brushed Nickel
- 3 12" Stem - Steel - Brushed Nickel
- 1 Sloped Ceiling Hardware - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990CH312460_-ALT)

Collection: Alturas
UPC #: 785652044373
Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Etched / White Inside	3	G560196-303			6 1/8	3 1/2				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	3/4			5 1/8		

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted	A19	Medium	9.5	9.5	120v	15000	800 230°	3000	90

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	3124603EN3-962	1	785652044373	21.5	12.75	21	3.331	10.9	250	Yes
NJ Pallet		18		48	40	73	81.111	196.2		No
NV Pallet		18		48	40	73	81.111	196.2		No