



| Model No | Input Voltage (VDC) | Lamp Power (Watt) | A | B | C | D | Max Continuous Length |
|--------------------|---------------------|-------------------|-----------|-----------|--------|-------|-----------------------|
| LV-HS-PD20-24V-30 | 24V | 4 W | 11 13/16" | 11 1/4" | 13/16" | 9/16" | 20' |
| LV-HS-PD20-24V-50 | 24V | 7 W | 19 11/16" | 19 1/8" | 13/16" | 9/16" | 20' |
| LV-HS-PD20-24V-100 | 24V | 13 W | 39 3/8" | 38 13/16" | 13/16" | 9/16" | 20' |
| LV-HS-PD20-24V-120 | 24V | 16 W | 47 1/4" | 46 11/16" | 13/16" | 9/16" | 20' |