



3MAVR52RZW: 52" Maverick II - Matte White



Dimensions:

- Diameter:** 52"
- Weight:** 10.4 lbs.
- Reverse Switch:** Remote Controlled
- Rev. Switch Location:** Remote Transmitter
- Motor Size:** 85.0 X 28.0
- Diameter of Housing:** 7.0
- Lead Wire Length:** 78 inches
- Remote Included:** Hand Remote
- Location of Receiver:** Canopy
- Remote Group(s):** ESSWC-7

Features:

- Includes a green, energy-efficient DC motor
- Specialty carved wood blades included
- Remote included for easy operation

Collection: Maverick II

UPC #: 014817586336

Finish: Matte White (RZW)

Blade Finish: Matte White

Blade Finish 2: Undefined

Material List:

Safety Listing:

- Safety Listed for Damp Locations
- Safety Listed for Damp Locations

Instruction Sheets:

- English (3MAVR52XX-CUL-ENG)
- French (3MAVR52XX-CUL-CF)

Blade Details:

Blade Group	Diameter	Included	RPM Hi	CFM Hi	Watts Hi	Amps Hi	RPM Med	CFM Med	Watts Med	Amps Med	RPM Low	CFM Low	Watts Low	Amps Low
	52	Yes		5889.37	27.08									

Mounting Options:

Mounting Type	Included	Item	Downrod Length	Downrod Diameter	Overall Height	Blade to Ceiling	Min. Ceiling Height	Canopy Style	Canopy Diameter
Downrod (Included)	yes		6.0	0.5	11.7	11.5	7.96		6.4

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	3MAVR52RZW	1	014817586336	32	13	10.25	2.468	15.9	70	Yes
NJ Pallet		25		48	40	70	77.778	397		No
NV Pallet		25		48	40	70	77.778	397		No