



Image File Name: F786-CL.jpg

| | |
|---------------------------------------|--------------------------------------|
| Item # F786-CL | UPC Code: 706411060731 |
| Product Family Name: Simple | Finish: Coal |
| Category: INTERIOR FAN | Category Type: Ceiling Fan |
| Certification 4009339 | |
| Patents: | |
| Notes: | |



MEASUREMENTS

| | | | |
|----------------------------------|--------------------------|-------------------|------------------------|
| Blade Finish: | Reversible Blades: | | |
| | No | | |
| Blade Material: | Slope: | | |
| ABS | Yes | | |
| Blade Sweep: | No. of Blades: | Blade Pitch: | Hanging Weight: |
| 44" | 3 | 14 DEGREES | 9.26 |
| Downrod 1: | Downrod 1 Outside Dia: | Downrod 2: | Downrod 2 Outside Dia: |
| 6 | .75 | | |
| Ceiling to Lowest Point: (Dim A) | Ceiling to Blade (Dim B) | Lead Wire: | Motor Size: |
| 12.75 | 11.25 | 8" | DC 123x30mm |

| | | | | | |
|-------------------|--------|----------|--------|----------|--------|
| | Low | Low/Med. | Medium | Med/High | High |
| RPM: | 51 | | | | 196 |
| Amps: | 0.06 | | | | 0.59 |
| Watts: | 3.89 | | | | 48.06 |
| CFM: | 1615.0 | | | | 5323.0 |
| CFM/Watts: | 415.17 | | | | 110.76 |

LAMPING

| | | | | |
|--------------------|--------------|----------|-------------------|-------------------|
| No. of Bulbs: | Light Type: | | | |
| 0 | | | | |
| Max Bulb Wattage: | Socket: | | | |
| | | | | |
| Light Kit: | Dimmable: | Ballast: | Rated Life Hours: | Uplight: |
| No | No | | | No |
| Bulb/LED Included: | Color Temp.: | CRI: | Initial Lumens: | Delivered Lumens: |
| | | | | |

GLASS

| | |
|--------------|-----------|
| Description: | Material: |
| Part No.: | Quantity: |
| Width: | Height: |
| | Length: |



SHIPPING

| | | | |
|---------------------|---------------------|--------------------------|--------------|
| Carton Width: | Carton Height: | Carton Length: | |
| 8.63 | 9.0 | 22.75 | |
| Carton Weight: | Carton Cubic Feet: | Small Package Shippable: | |
| 11.0 | 1.023 | Yes | |
| Master Pack Width: | Master Pack Height: | Master Pack Length: | |
| | | | |
| Master Pack Weight: | Master Cubic Feet: | Multi-Pack: | Master Pack: |
| | | 1 | 1 |



FAN CONTROLS

| | | |
|---------------------|-------------------------------|-----------------------------|
| Pull Chain Control: | Works with Remote Control: | Works with Wall Control: |
| No | Yes | Yes |
| Reversible: | Included Remote Control: | Included Wall Control: |
| Yes | RC400 | |
| | Compatible Remote Control(s): | Compatible Wall Control(s): |
| | | WC400 |



Wet Location



ETL Intertek

WARNING: Handling this product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. Wash hands with soap and water after installing, handling, cleaning or otherwise touching this product. For more information go to: www.P65Warnings.ca.gov.

For additional information, please contact Customer Care: 1-800-221-7977 | Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties.