



**MCR
SAFETY**

N9696

Ninja

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® Lite features an 18 gauge blue nylon shell and black PU coated palm and fingertips.

FEATURES:

- 18 Gauge Athletic Grade Nylon Shell
- PU Coated Palm and Fingertips
- CE Score 4131
- Feather-light second skin feeling
- 30% Lighter for Greater Tactile Sensitivity

APPLICATIONS:

Automotive Assembly, Assembly Line Production, Automotive , Carpentry, Construction, Farming, Furniture industry, Janitorial , Landscaping, Material Handling, Mechanics, Shipping / receiving, Warehousing, Manufacturing



TECHNICAL DATA FOR: N9696L

Series	Ninja	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	3
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	18 Gauge	ANSI Abrasion	ANSI Abrasion 3
Material	Nylon		
Made In	Sri Lanka		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved



MCR
SAFETY

N9696

Ninja

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N9696M	Medium	11.614	3.425	2.559	10.464 lb.	0.872
N9696XL	X - Large	12.598	3.898	2.756	11.388 lb.	0.949
N9696XS	X - Small	10.630	3.228	2.362	9.324 lb.	0.777
VPN9696S	Small	0	0	N/A	7.488 lb.	0.052
N9696S	Small	11.142	3.307	2.480	9.984 lb.	0.832
N9696L	Large	12.126	3.740	2.677	11.028 lb.	0.919
VPN9696XL	N/A	0	0	N/A	8.352 lb.	0.058
VPN9696L	Large	0	0	N/A	8.064 lb.	0.056

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2019 MCR Safety - All Rights Reserved