



Representative



Illustration

**Catalog Number:** 6H5 B  
**Product ID:** 7TAA015000R0033  
**UPC Number:** 78599150496  
**EAN Number:** 05415022191523  
**Status:** Active

Hanger, Conduit and Pipe, EMT Size 2 Inches, Rigid Conduit or Pipe 2 Inches, Steel, with Bolt

- Accommodates 1/2 Inch through 4 Inch EMT or rigid conduit.
- Can be used for either vertical or horizontal installation.
- 6HTB Series have a built-in nut so there are less parts to handle or drop.
- Installs easily with a screwdriver.

### North American Specifications (UNSPSC)

UNSPSC	39121701 Electrical hangers
IGCC	5026 Electrical hangers
Brand Name	Steel City
Type	Conduit Hangers
Special Features	Accommodates 1/2 in. through 4 in. EMT or rigid conduit.
Application	For use with EMT and Rigid conduit or pipe
Standard	UL E160899
Size	2
Material	Steel
Finish	Galvanized

### European Specifications (ETIM)

ETIM	EC002470 Mounting clamp for cable protection tubes
Material	Steel
Rotatable	N

### Packaging

Outer Quantity	50
Outer Dimensions (inches)	17x11.5x5.25
Weight Uom	25 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)