



Outdoor Color Preference[®] Flushmount

830lm | 120-277VAC | Model 54466101 | Part FME-10-802-MV-N-N-B


- > Energy Saving 12.5 Watt Integrated LED
- > Uses 79% Less Energy than Equivalent 60 Watt Incandescent Bulb
- > Soft White 3000K CCT
Cool White 4000K CCT
Daylight 5000K CCT
- > Lasts 45 years or 50,000 Hours Continuous Use
- > Maintenance Free — No Bulb Replacements
- > 5 Year Limited Warranty



SPECIFICATIONS

Model	54466101
Part	FME-10-802-MV-N-N-B
Description	Outdoor Color preference [®] Flushmount
Input Voltage (VAC)	120-277
Dimmability	Non-Dimmable
Wattage	12.5
Average Rated Life¹	50,000 hours
Typical Lumens²	830
CCT³	3000K/4000K/5000K
Location Rating	UL Damp
CRI⁴	80
Beam Angle Operating	120
Temperature	Min -4°F (-20° C), Max 95°F (35° C)
Power Factor	>0.9
R9	20
DUV	-0.00267
CBCP	328
Operating Frequency (Hz)	50/60

1 Hours lifetime with 70% lumen maintenance
 2 Thermally stable typical lumens (±10%)
 3 Thermally stable CCT (±10%)
 4 Color rendering index/Ra



All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: YN84-URRESA (8/29/2017)

Model Number: 54466101 (#11-01-10)

Type: Luminaire - Other

TO ORDER:
www.ETiSSL.com
 Call: 1.855.ETi.SSLI
 1.855.384.7754





Outdoor Color Preference[®] Flushmount

830lms | 120-277VAC | Model 54466101 | Part FME-10-802-MV-N-N-B

SHIPPING INFORMATION

Model	54466101
Part	FME-10-802-MV-N-N-B
UPC	849489006468
Product Dimensions (L x W x H in.)	10.43 x 10.43 x 3.94
Product Dimensions (L x W x H cm.)	26.5 x 26.5 x 10.0
Product Weight (lbs.)	1.83
Inner Carton Quantity	N/A
Inner Carton Bar Code	N/A
Inner Carton Dimensions (L x W x H in.)	N/A
Inner Carton Dimensions (L x W x H cm.)	N/A
Inner Carton Weight (lbs)	N/A
Master Carton Quantity	6
Master Carton Bar Code	50849489006463
Master Carton Dimensions (L x W x H in.)	26.77 x 11.26 x 11.54
Master Carton Dimensions (L x W x H cm.)	68.0 x 28.6 x 29.3
Master Carton Weight (lbs)	14.06
Pallet Quantity	144

AVAILABLE ACCESSORIES

Model	Description
95446610101	Diffuser Lens

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, Please see www.etissl.com/fcc15b

TO ORDER:
www.ETiSSL.com
Call: 1.855.ETi.SSLI
1.855.384.7754

ETi Solid State Lighting, Inc.
720 Corporate Woods Parkway
Vernon Hills, IL 60061
Phone: 855.384.7754
Fax: 847.383.6256