


P38LED201-6PK

CRI 80 3000K 1400Lumens LED Reflector



The high performance LED PAR bulb.
 Perfect for track and recessed light fixtures.
 For commercial or home lighting applications
 Easy to use - designed in traditional bulb shapes and fits easily into existing fixtures

Performance



- LED PAR bulb is designed to provide 25000 hours of life,18Watt.
- Energy-saving & Super bright, saving 85% energy compared with traditional halogen lamp
- UL & ES compliant.

Construction

- Rotary Extrusion Aluminum for excellent heat dissipation
- Dimmable.

Installation

- Rated for indoor/outdoor use
- Suitable for damp/wet locations.
- Can't be used in totally enclosed fixtures
- Not for use with emergency exit fixtures or emergency exit lights
- Size:Φ4.8"(122mm)*H5.2"(132mm)



Specifications

Category	Light Bulb	Inner Package Length (Inch)	15.04
Bulb Shape	PAR38	Inner Package Width (Inch)	10.16
Bulb Base Type	E26	Inner Package Height (Inch)	6.1
Bulb Base Finish	Chrome	Inner Package Weight Per Unit (Lbs)	5.38
Color Temperature	3000K	Inner Package Weight Per Unit (Lbs)	6
Beam Angle	40°		
Finish	Silver		
CRI	80		
Average Life (Hours)	25000		
Estimated Yearly Energy Cost (11 ¢/Kwh)	2.17		
Life Based On 3Hrs/Day (Years)	22.83	Lamp Type	PAR38
Product Length (Inch)	N/A	Dry/Wet/Damp	Wet
Product Width (Inch)	4.8	Energy Star	YES
Product Height (Inch)	5.2	Power Factor	>0.9
Product Extension (Inch)	N/A	Current	160mA
Product Weight Per Unit (Lbs)	0.57	Lumen/Watt	78
Dimmable	YES	Warranty (Year)	3
Watts	18W	DLC (Yes/No)	No
Watt Equivalent	90W	Input Voltage	120V
Lumens	1400	Housing Material	Aluminum
Certification (UL/ETL/FCC)	UL	Lens	Plastic
Individual Box Length (Inch)	4.88	Led Type	Seoul
Individual Box Width (Inch)	4.88		
Individual Box Height (Inch)	5.71		
Individual Box Weight Per Unit (Lbs)	1.09		