



CorePro LEDtube PL 4pin 2pin

12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Product data

General Information		Warm Up Time to 60% Light (Nom)	
Cap-Base	G24Q/GX24Q [G24q/GX24q]		0.5 s
Main Application	Industrial	Power Factor (Nom)	0.9
Nominal Lifetime (Nom)	50000 h	Voltage (Nom)	25-55 V
Switching Cycle	50000X	Temperature	
B50L70	50000 h	T-Ambient (Max)	45 °C
Light Technical		T-Ambient (Min)	-20 °C
Color Code	830 [CCT of 3000K]	T-Storage (Max)	65 °C
Initial lumen (Nom)	1400 lm	T-Storage (Min)	-40 °C
Luminous Flux (Rated) (Nom)	1400 lm	Controls and Dimming	
Correlated Color Temperature (Nom)	3000 K	Dimmable	Yes
Color Consistency	<6	Mechanical and Housing	
Color Rendering Index (Nom)	82	Product Length	100 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Energy Saving Product	Yes
Input Frequency	20000-100000 Hz	Approbation Marks	UL certificate RoHS compliance KEMA Keur certificate DLC compliance
Power (Rated) (Nom)	12 W		
Lamp Current (Max)	500 mA		
Lamp Current (Min)	150 mA		
Starting Time (Nom)	0.5 s		


CorePro LEDtube PL 4pin 2pin

Product Data

Order product name	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1
EAN/UPC - Product	046677476113
Order code	476119
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

Material Nr. (12NC)	929001820204
Net Weight (Piece)	0.082 kg
Model Number	9290018202


Dimensional drawing




PLED 120V 12-32W 1400lm 3000K G24/Gx24

Product	D1	D2	A1	A2	A3
12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm


Photometric data



LEDtube PLC 400mm 16-5W 2G11 830 2000lm





LEDtube PLC/T 12W G24Q 830 32V DIM



LEDtube PLC/T 12W G24Q 827 32V DIM



CorePro LEDtube PL 4pin 2pin

Lifetime




LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM

LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM



LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM

LEDtube PLC/T 12W G24Q 827-840 32H-32V DIM



LEDtube PLC/T 12W G24Q 827-840 32V DIM

CorePro LEDtube PL 4pin 2pin

