



S8552

4.5W CFC/LED/27K/CL/120V
 4.5 watt CA11 LED; Clear; Candelabra base; 2700K; 350 lumens; 120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 40 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures



S8552

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S8552	045923085529	120	4.5	40W	CA11	Candelabra	E12

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
4.5W CFC/LED/27K/CL/120V	Dimmable	Compatible dimmers for S8552	Clear	4-11/16"	1-3/8"	350	15000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
2700	Warm White	90+	360	-20C (-4F) to a maximum of +45C (+113F)	24/1	Box	ENERGY STAR

CEC Status	RoHS Compliant	Fixture Type	UL Classification	Warranty
Lawful for sale in California	Yes	Enclosed Rated	cULus - Damp Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

