




RIGID-IMC FITTINGS

MALLEABLE IRON THREADLESS INSULATED GROUNDING BUSHINGS

[Download
Specification Sheet
\(\[https://www.sepco-usa.com/wp-content/uploads/2017/03/page_057.pdf\]\(https://www.sepco-usa.com/wp-content/uploads/2017/03/page_057.pdf\)\)](#)



[Print](#)



25BI4LSS

Trade Size	2"
GROUNDING LUG CAPACITY	#14-#4
Dim A	2.81
Dim B	0.85
Dim C	0.85

Unit Pack **25**

Master Pack **250**

Lbs. / 100 Pcs. **28**

UPC **29405**

Competitor Part **IB-200SL-4,**

Number **HGLS6, IBC-**

200LS-4AC,

336MSS

APPLICATION

Used with a locknut to terminate threadless rigid and IMC conduit to a box or enclosure and to provide a smooth pulling surface.

Thermoplastic liner prevents damage to wire insulation. Liner rated at 150°C.

FEATURES

The plastic liner won't chip, crack, swell or shrink. It resists corrosion, chemicals, and temperature extremes. Set-screw provided with each fitting locks bushing in any desired position. UL Listed for use with Copper or Aluminum Grounding Conductors.

STANDARD**MATERIALS**

Malleable Iron/Open side tin plated aluminum lug.

STANDARD**FINISH**

Zinc plated

UL LISTED

E93683

