







ULTRATHIN CANOPY SURFACE MOUNT 45W



- Features:
- Thin Appearance
 - Good Heat Dissipation
 - Convenient Installation
 - Pendant or Surface Mount
 - Long Life high Efficiency LEDs

Part#	Housing Color	Wattage	Lumens	CCT	Voltage	Dimming	Lumens/Watt	DLC#
71600B	Bronze	45W	5000	4000K	120-277	0-10V	110	PLYW1FZ3V46A

PHOTOMETRY





ULTRATHIN CANOPY SURFACE MOUNT 45W

Technical Specifications:

Electrical:

Input Voltage: 120 thru 277
Current: .378A@120V; .189A@277V
Frequency: 60Hz
Power Factor: $\geq .9$

Product Parameters:

45 Watts
Efficacy: 110 lumens per watt
50,000+ LED Life Span
CCT: 4000k (Neutral White)

Chromaticity Measurements:

Beam Angle: 140°
CRI: ≥ 70
R9: -26.4
DUV: 0.0042
Chromaticity (x,y): $x=.3764$; $y=.3833$
Chromaticity (u,v): $u=.2199$; $v=.3359$

Component Specifications:

LED: SSC3030
Driver: 120-277V 50-60HZ
Driver Output Volts: 120-277
Driver Output Amps: 132mA
Surge Protection: 10000V

Dimming: 0-10V

Operating Temperature:

Minimum Starting -31° - 122° F

Construction:

Housing: Aluminum Housing
Powder Coat Bronze Finish
IP Rating: IP65 Wet Location Rated
Lens Material: Prismatic Polycarbonate Lens
Mounting: Ceiling Mount
(Drywall / Sheetrock)

Listings: ETL

DLC#: PLYW1FZ3V46A

Carton Qty: 1

Weight: 8 lb

Warranty:

Morris Products carries a 5 year warranty from date of purchase against defects in materials and workmanship (assuming normal and proper usage).