



Illustration

Catalog Number: D 255
Product ID: 7TAA004750R0000
UPC Number: 78599176887
Status: Active

Concrete Insert, Total Length 3-3/4 Inches, Width 3-11/32 Inches, Depth 1-5/8 Inches, Steel, For 1/4 Inch - 7/8 Inch Hanger Rod and 1/4 Inch - 1/2 Inch Pipe

North American Specifications (UNSPSC)

UNSPSC	30101804 Steel channels
IGCC	2577 Steel channels
Brand Name	Kindorf
Type	Concrete Inserts & Accessories
Special Features	An insert with a knockout saves covering the slot or covering the opening.
Application	Accommodates hanger rod sizes from 1/4 in. through 7/8 in. by means of a B-914 insert nut.
Material Composition	Steel
Finish	Galv-Krom/Standard
Color	Gray

Packaging

Outer Quantity	50
Outer Dimensions (inches)	13.1x9.7x10
Weight Uom	50 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com