

Project:

Type:

Prepared By:

Date:



UPC: 19813750668



Features and Benefits

REFLECTOR REPLACEMENT - Replacement for incandescent and halogen R reflector lamps

ENERGY SAVINGS - Save up to 85% on energy

25,000-HOUR LIFESPAN - Long-life product

DAMP RATED - Suitable for damp locations

ENCLOSED FIXTURE RATED - May be used in both enclosed and open fixtures

DIMMABLE - Compatible with most common dimmer models

SHATTERPROOF - Plastic lamps for rugged applications

110°+ BEAM ANGLE - Wide beam angle for maximum light distribution

80 CRI - Ideal for general lighting applications

Technical Specifications

Product Type	Reflector
Bulb Shape	R20
Wattage	7W
Wattage Equivalency	50W Incandescent
Typical Lumen Output	525
Efficacy	75 lm/W
Color Temperature	2700K Soft White
CRI	80
Base Type	E26
L70 Lifespan	25,000 hours
Operating Temperature	-20°C - 40°C
Dimmable	Yes, down to 10%
Beam Angle	110°
Warranty	3-Year, No-Compromise Warranty
For Use in Emergency Fixtures	No
For Use Outdoors in Open Fixtures	No


Electrical Characteristics

Input Voltage	120V
Power Factor	0.9
Flicker	<30%

Listings

UL Listed	Yes
ENERGY STAR V2.0	This product is ENERGY STAR® Version 2.0 Certified
Energy Star ID	2329463
CEC Status	Not lawful for sale in California

Light Distribution



Case and Pallet Dimensions

	QTY	LENGTH	WIDTH	HEIGHT
CASE	10	13.2	5.5	4.4
PALLET	2500	46.3	39.6	35.3

Dimension

