

## VS6704-PW: 4 - Light Vanity Fixture

### Dimensions:

Length: 24 1/2"      Extends: 7 1/4"  
 Height: 8"      Wire: 8"  
 Weight: 6.38 lbs.      Connection: Mounted To Box

### Bulbs:

4 - Medium A19 100w Max. 120v - Not included

### Features:

•

### Material List:

### Safety Listing:

Safety Listed for Damp Locations / IC  
 Safety Listed for Damp Locations / IC

### Instruction Sheets:

English (2003\_2031)



Collection: Bristol

UPC #:014817291940

Finish: Pewter (PW)

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate				6		
Back Plate				6	5 1/4	2 7/8

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frts. Class	UPS Ship
Individual	VS6704-PW	1	014817291940	25	10	10	1.447	9.9	125	Yes
NJ Pallet		36		48	40	68	75.556	356.4		No
NV Pallet		42		48	40	75	83.333	415.8		No