

WAC LIGHTING

Fixture Type: _____

Catalog Number: _____

Project: _____

Location: _____

Oculux 2"

11W 0° - 35° Adjustable Round

Model	Beam	Color Temp & CRI	Lumens	CBCP	Finish
R2BRA-11	F 45°	927 2700K - 90	955	1349	BN Brushed Nickel WT White
		930 3000K - 90	955	1349	
		930 3000K - 90	1005	1420	
	N 25°	927 2700K - 90	930	2549	
		930 3000K - 90	930	2549	
		930 3000K - 90	980	2683	
	S 15°	927 2700K - 90	860	4293	
		930 3000K - 90	860	4293	
		930 3000K - 90	935	4666	

Example: **R2BRA-11-F927-BN**

DESCRIPTION

Oculux 2" is an architectural grade recessed downlight with trim, LED light engine, and configurable housing ready to install as an IC-Rated New Construction or Remodel all-in-one unit. Oculux is Energy Star Rated and CEC Title 24 Compliant with Wet Location listing which means it can be installed in a broad range of applications. 35° visual cutoff provides superb glare reduction. Available in Round or Square open reflector and adjustable trim options.

FEATURES


- Cutout 3 1/16"
- Single spot light source
- Ceiling thickness: 1/2" - 1"
- Sold as New Construction, may be reconfigured in the field for Remodel
- Driver concealed within the fixture
- 5 year warranty

SPECIFICATIONS

Construction:	Die-cast aluminum trim with aluminum heat sink
Power:	11W
Input:	120 VAC, 50/60Hz
Dimming:	TRIAC: 100-5%, ELV: 100-5%, 0-10V: 100-5%
Light Source:	Integrated LED 3 Step Mac Adam Ellipse
Cut Out:	3 1/16"
Finish:	Electrostatically Powder Coated Brushed Nickel, White
Ceiling Thickness:	1/2" - 1"
Operating Temp:	-4°F to 104°F (-20°C to 40°C)
Standards:	ETL, cETL, Damp Location Listed, Energy Star 2.0, Title 24 JA8-2016 Compliant, IC, Airtight



FINISHES



LINE DRAWING

