



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Arrow Hart Color Coded Locking Receptacle

AHCL1630R

UPC:032664758591

### Dimensions:

- **Height:** 3.64 IN
- **Length:** 1.62 IN
- **Width:** 1.06 IN

**Weight:** .33 LB

### Warranties:

### Specifications:

- **Special Features:** Voltage Color Coding
- **Type:** Locking Receptacle
- **Allowable Wire Size:** #14-8 AWG
- **Amperage Rating:** 30A
- **Application:** Industrial
- **Voltage Rating:** 3Ø 480 V
- **Wiring Method:** Back & Side
- **Color:** Red, Black
- **Design Type:** Ultra grip
- **Face/Body Material:** Glass filled Nylon
- **Nema Configuration:** L16-30
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Four-wire
- **Material:** Glass-filled Nylon
- **Operating Temperature:** -40°C (w/o impact) to 70°C (-40°F to 158°F)

### Supporting documents:

- [ah-color-coded-L16-30-locking-devices-spec-sheet.pdf](#)

### Certifications:

- CSA Certified
- UL Listed
- NOM



- Federal Specification Classification 6233 01

**Product compliance:**

- RoHS Compliant
- NAFTA

---

© 2016 Eaton. All rights reserved.