



Powering Business Worldwide

pe.eaton.com

Eaton Arrow Hart Color Coded Locking Receptacle

AHCL530R

UPC:032664758683

Dimensions:

- **Height:** 3.64 IN
- **Length:** 1.62 IN
- **Width:** 1.12 IN

Weight: .33 LB

Warranties:

Specifications:

- **Special Features:** Voltage Color Coding
- **Type:** Locking Receptacle
- **Allowable Wire Size:** #14-8 AWG
- **Amperage Rating:** 30A
- **Application:** Industrial
- **Voltage Rating:** 125V
- **Wiring Method:** Back & Side
- **Color:** Yellow, Black
- **Design Type:** Ultra grip
- **Face/Body Material:** Glass filled Nylon
- **Nema Configuration:** L5-30
- **Number Of Poles:** Two-pole
- **Number Of Wires:** Three-wire
- **Material:** Glass-filled Nylon
- **Operating Temperature:** -40°C (w/o impact) to 70°C (-40°F to 158°F)

Supporting documents:

- [ah-color-coded-L5-30-locking-devices-spec-sheet.pdf](#)

Certifications:

- CSA Certified
- UL Listed
- NOM



- Federal Specification Classification 6233 01

Product compliance:

- RoHS Compliant
- NAFTA

© 2016 Eaton. All rights reserved.