

## DESCRIPTION

The COR Series offers quality and value with a compact and attractive LED based remote emergency light. The white or black base-plate and lamp-heads are made of high impact UL flame rated thermoplastic. Lamp-heads are fully gasketed and weatherproof to ensure operation in wet environments. The lamp heads are fully adjustable and glare-free. The remote lamps are driven by the Compass remote capacity Exit, Combo or Emergency Light.

## APPLICATION

The COR Series can be applied over path of egress doors and in areas affected by rain, moisture and condensation.

## COMPLIANCES

UL924 Damp Listed  
 NFPA 101 and NFPA 70  
 OSHA

## WARRANTY

2 year full unit warranty



tradeSELECT®

## FEATURES


- Single or Double lamp-head outdoor remote with base
- LED life-cycle of more than 10 years
- Quick installation
- Fully adjustable lamp-heads
- Fully gasketed for application in wet environment
- White or Black Color

## ORDERING GUIDE

Catalog Number	Description	Voltage	Lamp Watts (Each)
<b>CORS</b>	Single LED outdoor remote white lamp-head with mounting base	3 VDC	1 Watt
<b>CORD</b>	Double LED outdoor remote white lamp-head with mounting base	3 VDC	1 Watt
<b>CORSB</b>	Single LED outdoor remote black lamp-head with mounting base	3 VDC	1 Watt
<b>CORDB</b>	Double LED outdoor remote black lamp-head with mounting base	3 VDC	1 Watt


Powered by Compass Exit, Combo or Emergency Light with Remote Capacity

## DIMENSIONS



### CORS

**Single Remote Carton Weight:** 1 lbs.  
**Master Carton Quantity:** 20 each



### CORD

**Double Remote Carton Weight:** 1.2 lbs.  
**Master Carton Quantity:** 20 each