

product

Die cast aluminum with two unique "flex-lugs" for wall or pole mounting of outdoor outlets, switches or floodlights. Ground screw and close-up plugs provided. Cubic capacity is 18.3 cu. inches.

Color: Black

Weight: 0.6 lbs

Project:

Type:

Prepared By:

Date:

Technical Specifications

Listings

UL Listing:

Suitable for wet locations.

Other

Outlet Box Construction:

Precision die cast aluminum.

Tap Size:

1/2"

Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Construction

Outlet Box Mounting Lugs:

16 gauge corrosion protected steel with Phillips Flat head mounting screws.


Ground Screw:

#10-24 Green corrosion protected steel slotted hex washer head screw provided in pre-tapped hole.

Hole Count:

3 Hole

Dimensions



Features

- "Flexi" mounting lugs can mount to top or side
- Green hex slotted washerhead ground screw in pre tapped hole
- Heavy die cast aluminum
- Two easy knockout mounting holes
- Versatile cover mounting system accepts most common covers
- Close-up plugs allow Phillips or slotted screwdrivers for easy installation