

# Combination Couplings

## Liquidtight to Rigid - Steel

### Features

- Liquidtight, raintight, oiltight
- NPSM thread
- Labor saving

### Applications

- Use to join liquidtight metal conduit (LFMC) to Rigid/IMC conduit between 2 different raceways
- Suitable for use in wet locations
- Raintight, concrete tight

### Standard Material

- Steel


### Standard Finish

- Zinc plated



E148716

UL standard 514B  
Fed.Spec. A-A-50553  
NEMA FB 1



Catalog Number	UPC	Size	Unit Carton	Ship Case	Weight/Case	Inches	
						A	B
50SLT	87323	3/8"	20	200	33	1.10	1.78
51SLT	87324	1/2"	20	200	29	1.17	1.78
52SLT	87325	3/4"	10	100	23	1.43	1.94
53SLT	87326	1"	5	50	18	1.76	2.19
54SLT	87327	1-1/4"	5	50	30	2.16	2.23
55SLT	87328	1-1/2"	-	12	8	2.38	2.62
56SLT	87329	2"	-	5	5	2.87	2.67