



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

YA36N  
 7818100210400  
 600 CU 1-HOLE LONG 1/2  
 Active

**Web Use**  
 BURNDY Product Line

Tongue Angle  
 Length (in)  
 Tongue Type  
 Barrell Style  
 Bolt Hole Size (in)  
 Barrel Type  
 Thickness  
 B Length (in)  
 Pad Width (in)  
 Strip Length

**Dimensional**  
 Straight  
 4.83  
 Standard  
 Chamfered  
 0.52  
 Long  
 0.27  
 2.69  
 1.74  
 2-3/4

Number of Holes

**General**

1  
 Copper Compression Lug, 1 Hole  
 w/o Inspection Window, 600  
 kcmil, 1/2" Stud, Long Barrel,  
 Electro tin Plated

Product Description

**Conductor(s)**

Flex (Class G) Size - Range  
 Flex (Class H) Size - Range  
 Flex (Class I) Size - Range  
 Copper Solid Size (Range)  
 DLO Size (Range)  
 Copper Stranded (Range)

N/A  
 N/A  
 N/A  
 N/A  
 N/A  
 600 kcmil

Type of Plating  
 Bolt Hole Size  
 Color Code  
 Plated (Yes or No)  
 Index Number  
 Product Material

**Physical**

Tin - Electro Plated  
 1/2  
 Green  
 Y  
 22,472  
 Copper

**Approvals / Certifications**

UL Listed  
 CSA Certified  
 ROHS Compatible  
 UL Recognized  
 CULUS

Y  
 Y  
 Compliant  
 N  
 N

**Documentation**

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175