

WRAP LED | 4' LED Ceiling Wrap

57521 / 57522


- Surface Mountable LED Wrap
- PMMA Acrylic Diffuser
- Dimmable with CL Triac dimmer
- Damp Location Rated
- L70 Project Life of 50,000 Hours
- Color Temperatures of 3000k/4000k
- Suitable for Closets according to NEC Section 410.8 & 410.16
- CRI 90+
- Energy Star
- Title 24 JA8 Compliant

Job Name : _____
Job Type : _____
Quantity : _____
Comments : _____



PRODUCT DESCRIPTION

The classic Wrap Around is updated with more efficient and uniformly lit LED technology. Safer than harmful fluorescent lighting and longer lasting as well. Meeting today's Energy Star and Title 24 requirements, this product is fully dimmable and achieves a color rendering over 90 without sacrificing light output.



MEASUREMENT

DIMENSIONS : 4"W x 48"L x 4.5"H

LAMPING

INPUT VOLTAGE : 120V
LUMENS : 3800
BULB : 40W LED
DIMMABLE : Triac CL
CRI : 90+

Model	Color Temp.
57521	4000K
57522	3000K

FINISH:

White (WT)



MATERIALS:

Acrylic + Steel

RATINGS:

ETL/cETL
Damp Location
Energy Star
Title 24 JA8 Compliant
Closets Rated: 410.8 & 410.16



ADDITIONAL:

RATED LIFE: 50,000 Hours

Always consult a qualified electrician before installing any lighting product



WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE | CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
4200 SHIRLEY DR. | ATLANTA, GA 30336

P. 626.956.4200 | F. 626.956.4225 | maximlighting.com