



TRADITIONAL Wall Light

60 Watt LED Die Cast Wall Light




PROJECT INFORMATION

Job Name: _____
 Fixture Type: 60 Watt LED Die Cast Wall Light
 Catalog Number: AWM60
 Approved by: _____

Dimensions

Weight: 9.25 lbs.



Electrical Specifications

- Input Wattage: 60.38W
- Efficacy: 122.07 LpW
- AC Input: 120/208/240/277 V
- Driver: Constant current, Class 2, 120-277VAC 50/60Hz
- Dimming: 0-10V

Housing Specifications

- Rugged traditional aluminum die-cast housing
- Lifespan: 100,000 hours
- Lens assembly is designed to provide high efficiency and to target the light where needed
- Installation: Fixture retains the same knock-out sizes and positions as previous models, reducing wiring costs

Testing

- LED luminaires have been tested by an independent laboratory in accordance with IESNA LM-79 & LM-80

Lighting Specifications

- Total Lumens: 7,371
- Color Temperature: 4500K
- Color Rendering Index: 80

Listings

- UL/cUL standards for wet locations
- DesignLights Consortium qualified luminaire, eligible for rebates from DLC member utilities

Options

- Photocontrol: For factory installed 120V button photo control add suffix PC to part number. For factory installed 208-277V button photo control add suffix PM to part number

Warranty

- 5-Year limited warranty

