

Catalog Number: 665 RP
Product ID: 7TAA003130R0003
UPC Number: 78599161862
Status: Active



Actual



Representative

Device Plate, Galvanized Steel, Duplex Receptacle, For use with Four Gang Recessed Service Floor Box, 126 Cubic Inches for Device Access and 40 Cubic Inches for Device Compartments, Length 5-3/4 Inches, Width 2-3/4 Inches, Depth 2-1/2 Inches, 3/4 Inch and 1-1/4 Inch Knockouts, Galvanized Steel, Delivers Power, Communications and Data from Standard Conduit with No Exposed Service Fittings

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121307 Floor boxes
IGCC	4432 Floor boxes
Brand Name	Steel City
Type	Recessed Service
Application	For use with 665 series floor boxes
Standard	UL E2969
Material	Steel
Knockouts	No

European Specifications (ETIM)

ETIM	EC000006 Cover plate for installation units
Length cover plate	146.05mm
Application	Sub-floor outlet box
Number of single openings	1
Type of fastening	Screwing
With label area	N
Suitable for label area	N
Material	Steel
Colour	Other

Packaging

Inner Quantity	1
Outer Quantity	4
Outer Dimensions (inches)	6x6.5x3.25
Weight Uom	31.25 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com