

[Print](#)




HID14/850/LED3 84303 LED HID RETROFIT BYPASS 14W 5000K NON-DIMMABLE 120- 277V E26


Product Number: 84303
UPC: 807154843039

[Log In for Price and Availability](#)

Specifications	Resources	Technical
Applications		Post Top, Wall Pack, Low Bay
Average Life (Hrs)		50,000
Base		E26
Beam Angle		Omnidirectional
Brand		ProLED
CRI		84
CSA		No
Color Temperature		5000
DesignLights Consortium		No
Dimmable		No
ENERGY STAR		No
Equivalent Wattage		70W
HTS code		8539500090
Initial Lumens		1904
Inner Carton Quantity		1
Input Current (Amps)		0.12
Input Frequency (Hz)		50/60
Markets		Commercial/Industrial
Master Carton Quantity		24
Maximum Overall Diameter		2.76
Maximum Overall Length		6.06
Nominal Length		6.06
Operating Position		Universal
Prod Code		HID14/850/LED3
Product Category		LED
Product Description		?LED HID RETROFIT BYPASS 14W 5000K NON-DIMMABLE 120-
Product Number		84303
Voltage (V)		100-277V
Warranty (Yrs)		5
Wattage (W)		14

Substitute Items:

 T896FR42/840/BYP2/RDC/LED 82877 LED T8 96 42W 4000K Double-End Byp Dimmable R17d ProLED

 HID15/850/MV2/LED 84003 LED HID RETROFIT BYPASS 15W 5000K NON-DI 277V E26 ProLED



Lamps

Ballasts

Luminaires

Pool & Spa

Company

Customer Care

Rebates

Contact Us

S



Norcross, GA 30071
Toll Free: 800.677.3334
Office: 770.242.3612
Fax: 800.880.0822
Email: customer care@halco.com



Copyright © 2020 - Halco Lighting Technologies

[Home](#)

[News](#)

[About Us](#)

[FAQ](#)

[Site Map](#)

[Privacy P](#)