


natural^{led}®

Product Engineering Spec

Product Spec			
Category	Commercial Wrap - Stairwell	PICTURE	
Item Code	9289		
Stock Code	LED-FXCWS38/48FR/840		
Mounting	Ceiling/Wall		
Housing Color	White + White PC Lens		

Electric Characteristics		Photometric Characteristics	
Rated Wattage (W)	38	Lumen (lm)	5275
Tested Wattage (W)	36.19	Efficacy (lm/w)	146
Input Voltage (V)	120~277	CRI	>80
Voltage Frequency (Hz)	50/60	CCT (K)	4000
Input Current (A)	0.34	Beam Angle (°)	100
Power Factor	>0.9	General Characteristics	
Replacement Wattage (W)	4x32W FL	Operating Temperature	-22°F~122°F
Surge protect level	4KV	Storage Temperature	-40°F~158°F
Dimmable	1-10V	IP rating	IP20
THD	<20%	Rated Life	50000 hrs
		Warranty	5 years

Product Dimensions		Suggested Accessory	
Weight (lbs.)	8.378	Microwave sensor	
Height (in)	3.15	Emergency Battery Backup Driver	
Length (in)	48	Wire Guard	
Width (in)	9		
Mounting Height (ft)			
Cable Length (ft)			

Qualifications			
UL/ETL	ETL	LM79	√
Energy Star		LM80	√
DLC	V4.4 Premium	IES File	√
CEC		FDA	
JA8		NEMA	
FCC	√	Dimmer List	
RoHS	√		

Comments: