

Eileen Collection
 Eileen 1 Light Wall Sconce - Brushed Nickel
 5096NI (Brushed Nickel)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____



Ordering Information

Product ID	5096NI
Finish	Brushed Nickel
Available Finishes	CH, CH, OZ, OZ, OZS, OZS, NI, NI
Collection	Eileen Collection

Dimensions

Extension	7.00"
Height from center of Wall opening	5.81"
Base Backplate	4.5 X 10
Weight	1.65 LBS

Specifications

Material	Steel
Diffuser Description	Satin Etched Cased Opal

Electrical

Voltage	120V
Input Voltage	Single(120)

Qualifications

Safety Rated	Damp
Warranty	www.kichler.com/warranty

Installation

Install Glass Up or Down	Yes
--------------------------	-----

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
# of Bulbs/LED Modules	1
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

Dimensions

Height	10.75"
Width	4.50"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	18-25W		