

Legge 1 Light Wall Sconce-Brushed Nickel

5051NI (Brushed Nickel)

Project Name: _____

Location: _____

Type: _____

Qty: _____

Comments: _____



Ordering Information

Product ID	5051NI
Finish	Brushed Nickel

Dimensions

Extension	5.00"
Height from center of Wall opening	3.75"
Base Backplate	4.75 X 7.75

Specifications

Material	Steel
Diffuser Description	Opal Etched

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Damp
Warranty	www.kichler.com/warranty

Installation

Install Glass Up or Down	Yes
--------------------------	-----

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
# of Bulbs/LED Modules	1
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

Dimensions

Height	8.00"
Width	4.75"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	23-30W		

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.