



TYPE: _____
 CATALOG #: _____
 NOTES: _____

Surface Mounted EF18, EF18D & EF18T Series

Thermoplastic PAR 36 Lamp Head

Features


- Thermoplastic construction with off-white finish; black (BK) optional
- Lamps (for alternate lamp selection, see lamp data sheet):
 Type H: Bi-Pin halogen
 Type I: High intensity tungsten (HIT) double contact bayonet base
 Type U: Sealed beam tungsten (not compatible with Ni-Cd battery)
 Type X: Sealed beam halogen (not compatible with Ni-Cd battery) or Type Z: High intensity incandescent wedge base
- Indoor use
- Available as a single, double or triple PAR 36 size lighting head
- Fully adjustable tool less aiming swivel head
- Specular parabolic reflector and prismatic lens for wide-beam, even light distribution
- Snap-out lens for easy lamp replacement.
- Surface Mount
- Includes a 5" round universal canopy plate with 3 knock-outs (supplied with 2 plugs) for use with single, double or triple head mounting
- Mounts to either a standard 4" octagonal or a single gang electrical box (4-gang plate for EF18T optional)
- UL924 Listed
- 3-year limited warranty
 Detailed warranty terms located at: www.emergi-lite.com/usa/files/EL_Warranty.pdf

Accessories (order as a separate item)

DESCRIPTION	PART NUMBER
Wire Guard	WG9-E

Dimensions

Dimensions are approximate and subject to change.



How to Order

SERIES	# OF HEADS	LAMP TYPE/WATTAGE	COLOR
EF18= PAR 36 remote head	Blank= Single head D= Double head T= Triple head	(H_) = Halogen Bi-Pin 20W max* (L_) = Tungsten wedge 25W max* (Z_) = Incandescent wedge 18W max* (U_) = Tungsten sealed beam 30W max* (X_) = Halogen sealed beam* 50W max** * For a complete list of available lamp types, please refer to the lamp data on pages 140-141 ** Use high temp enclosure (white or gray metal head)	Blank= Off white BK= Black

Example: EF18D(ZD)BK