

Hatteras Bay Collection
56 Inch Hatteras Bay Fan OBB
 300018OBB (Oil Brushed Bronze)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____

Product Information


Product ID	300018OBB
Finish	Oil Brushed Bronze
Blade Finish	Walnut/Cherry
Collection	Hatteras Bay Collection

Airflow, Power and Efficiency

Speed	RPM	CFM	CFM/ Watt	Amps	Watts
High	149	5515	69	.66	80
Med	97	3670	94	.53	39
Low	52	1895	135	.35	14



Dimensions



Downrod	A	B	C	D
1.00 OD X 12.00	22.50	18.50	15.25	6.63

Available Finishes

Finish	Fixture	Glass	Blade 1	Blade 2

Specifications

Number of Blades	5
Blades Included	Yes
Blade Pitch	14 Degrees
Blade Sweep	56"
Blades Reversible	No
Blade Material	WOOD
Optional Blades Available	No
Downrod 1	1.00 OD X 12.00

3 Speed Cooltouch Full Function - In project applications using multiple ceiling fans, alternative remote controls may be required. Please contact Kichler Advanced Product Solutions at 844-542-4537 to confirm your project requirements.

Primary Control System	
Remote Included	Yes
Wall Control Included	No
Low Ceiling Adaptable	Yes, Dual Mount Included
Lead Wire Length	78.00"
Motor Size	188MM X 25MM
Motor Type	AC

Downlight

Downlight Included	Yes
Light Source	Incandescent
Downlight Bulb Included	Included
Downlight Bulb Type	T3

Hatteras Bay Collection

56 Inch Hatteras Bay Fan OBB

300018OBB (Oil Brushed Bronze)

Project Name: _____
 Location: _____
 Type: _____
 Qty: _____
 Comments: _____

Finish	Fixture	Glass	Blade 1	Blade 2
Burnished Antique Brass	300018BAB	FRESNEL LENS	POPLAR BURL	ELM BURL
Brushed Stainless Steel	300018BSS	FRESNEL LENS	MEDIUM OAK	DARK OAK
Oil Brushed Bronze	300018OBB	FRESNEL LENS	WALNUT	CHERRY
Distressed Black	300018DBK	FRESNEL LENS	WALNUT	CHERRY

# of Bulbs/LED Modules	4
Watts	80/39/14
Max or Nominal Watt	40W
Glass Description	Fresnel Lens
Optional Light Kit Available	No

Safety Listings & Certifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Control Options

Product ID	Descr
370038MULTR	Wall Transmitter F-Function
371045MUL	56K Wall Control System Full F

Installation

Installation requirements	The electrical junction box and support structure must be securely mounted and capable of reliably supporting a minimum of 50 pounds. Use only ETL/UL listed electrical junction boxes marked ""For Fan Support""
Electrical Requirements	120V 60Hz AC
Hanging Weight	33 LBS
Minimum Distance Between Bottom Of Fan Blade To Floor	7.5 feet