



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker

QBGF2050

UPC:786679370056

Dimensions:

- **Height:** 3 IN
- **Length:** 5.8 IN
- **Width:** 4.6 IN

Weight:.85 LB

Notes:HACR rated

Warranties:

- 1 year

Specifications:

- **Type:** Quicklag
- **Special Features:** 5 mA Trip Sensitivity
- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120V
- **Mounting:** Bolt-on
- **Trip Type:** Non-Interchangeable
- **Circuit Breaker Type:** QBGF

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

Certifications:

- UL 489

Product compliance: No Data



