



# Rebar Grounding Clamp, Perpendicular – EK17 (710365)



- Universal use for rebar, rods or pipes
- Lay-in feature cuts installation time
- Bronze alloy construction with Stainless Steel 304 screws
- Approved for direct burial in earth and concrete



Part Number	EK17
Article Number	710365
Material	Bronze Stainless Steel 304 (EN 1.4301)
Connection Type	Perpendicular
Conductor Size	#10 Solid - #2 Solid 5.5 mm <sup>2</sup> Stranded - 25 mm <sup>2</sup> Stranded
Ground Rod Diameter, Actual (Ø)	12.7 – 25.4 mm
Water Pipe Size (Ø)	12.7 – 25.4 mm
Rebar Size, Metric	12 – 25 mm
Rebar Size, US	#4 – #8
Rebar Size, Canada	10M – 25M
Certifications	cULus
Standard Packaging Quantity	50 pc
UPC	78285657558
EAN-13	8711893041705

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

#### WARNING

Pentair products shall be installed and used only as indicated in Pentair's product instruction sheets and training materials. Instruction sheets are available at [erico.pentair.com](http://erico.pentair.com) and from your Pentair customer service representative. Improper installation, misuse, misapplication or other failure to completely follow Pentair's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2018 Pentair All rights reserved

Pentair, CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH and LENTON are owned by Pentair or its global affiliates.

All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.