



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Thermal-Magnetic Circuit Breaker

QBHW3015H

UPC:786679393154

### Dimensions:

- **Height:** 4.9 IN
- **Length:** 3.8 IN
- **Width:** 3.1 IN

**Weight:**1.15 LB

**Notes:**HACR rated

### Warranties:

- 1 year

### Specifications:

- **Type:** Quicklag
- **Amperage Rating:** 15A
- **Interrupt Rating:** 22 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V
- **Mounting:** Bolt-on
- **Trip Type:** Non-Interchangeable
- **Circuit Breaker Type:** QBHW
- **Quantity:** 8

### Supporting documents:

- [Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data



